



Air motor and mixing head is different from illustration

## Details:

- Pump Assembly Comet2/B, 65 ml/cycle, 5:1
- Also recommended for filled resin systems, thanks to self adjusting PTFE packings in the resin pump
- Peroxide pump with spindle adjustment, Ratio 1,0 to 3,5%
- Visual peroxide flow control for peroxide
- Filter system peroxide
- Mixing head with static mixer and flush device
- Pneumatic stroke counter
- Drum suction assembly for resin
- Trolley with Mast/Boom
- Tool kit in tool box
- Compressed air hose 10m with coupling
- Clear design, easy to operate
- Individual configuration possible

Seite / Page	Technische Änderungen vorbehalten!	Rev5-03.01.2013
1 / 3	Technical Modifications reserved!	Ersetzt / Replaces: Rev4-27.06.2012




*Peroxide pump with spindle adjustment*




*Operating panel with flow control*



*Stroke counter*



*RTM mixing head*



*Air Motor of Resin Pump*

Seite / Page	Technische Änderungen vorbehalten!	Rev5-03.01.2013
3 / 3	Technical Modifications reserved!	Ersetzt / Replaces: Rev4-27.06.2012